


Panamatic Optima 2 Waste Height


Range between:-

370 mm Maximum
260 mm Nominal
180 mm Minimum

to centre of pipe



Panamatic Optima 2 : Product Data



The Fulcrum, Vantage Way, Poole, Dorset BH12 4NU
tel: +44 (0) 1202 731555 | fax: +44 (0) 1202 731666
info@ddcdolphin.co.uk

www.ddcdolphin.co.uk

DDC Dolphin, Pulpmatic, Panamatic, Incomatic, Hygenex, MicrobeSafe are Registered Trademarks



Hands free operation

The Panamatic Optima 2

Washer disinfector with optimal performance clearing workloads quickly and effectively

Designed for optimal performance with both hot and cold wash cycle before disinfection, the Panamatic Optima 2 has a large capacity and can process two bedpans and two urine bottles at a time and can easily accommodate large bowls. It will help clear workloads quickly and effectively, saving time and cutting costs. With an increased number of more efficient cleaning nozzles and an increase in water jet pressure the wash performance has been greatly improved, and with better washing and temperature control, the overall cycle-time has been reduced for quicker turnaround.

Patented hands free operation - The Panamatic Optima 2 also benefits from our patented completely hands free open and close mechanism operated by means of a foot cup at the base of the machine and a top mounted optical sensor to close and start the machine. This makes the Panamatic Optima 2 not only more convenient, but also more hygienic to use than other pan washer disinfectors and greatly reduces the potential for cross contamination.

Automatic Disinfection - Thermal disinfection complies with the very latest standards and guidelines, including HTM2030

Easy service programme – Service support is provided by our own specialist and highly skilled engineers and we offer a choice of fully comprehensive service contracts focused on individual customer needs.



MicrobeSafe[®]
Antimicrobial Surface

Key Features

Patented hands free open and close operation

Dual antimicrobial action

Large capacity

Hot prewash cycle

Automatic disinfection

Top loading

Easy to use

Easy to install

Easy service programme

Due to a policy of continuous development and improvement the right is reserved to supply products which may differ slightly from those described in this brochure

General	
Stainless Steel grade:	304
Dimensions: w x h x d	500 x 1042 (±3) x 600 mm
Weight:	Dry 55kg
Capacity:	2 pots + 2 urine bottles
Operation cycle time:	8 minutes
Decibel rating:	53.5 dba
Electrical	
Voltage: 110V	N/A
Voltage: 230V	50Hz dedicated 13A breaker
Voltage:230V	60Hz dedicated 13A breaker
Voltage: 415V	N/A
Cable connection: 230V	3 core sheathed x 1.5mm ² , 2m long
Cable connection: 415V	N/A
Circuit Protection:	30mA RCD, GFI, IEC60364 compliant
Rated power input:	2.55kW
Electrical consumption per cycle:	0.17kW
Steam generator power:	2.5kW
Motor power:	N/A
Pump power:	0.75kW
Water	
Water connection:	¾" BSP male fittings required
Water pressure:	Hot & cold water ¾" 0.5-10 bar
Water flow rate (Min):	12 Litres per minute at 1 bar
Water tank capacity:	20 Litres
Water consumption per cycle:	42 Litres
Waste connection:	N.B. 75mm (3")
Overflow connection:	22mm
Disinfection	
Recommended disinfection detergents:	EcoWash+ or EcoWash+ Ultimate
Disinfection tank volume: (external)	5 Litres
Disinfection dosing per cycle:	30 Millilitres